




SIGMA QUALITY CONTROL TEST PROCEDURE

Product Information

Enzymatic Assay of THROMBIN (EC 3.4.21.5)

PRINCIPLE:



CONDITIONS: T = 37°C, pH 7.35

METHOD: Fibrometer

REAGENTS:

- A. 143 mM Diethyl Barbiturate and 143 mM Sodium Acetate Solution (Soln A)
(Prepare 275 ml in deionized water using Sodium Acetate, Trihydrate, Sigma Prod. No. S-8625, and Barbitol, Sodium Salt, Sigma Prod. No. B-0500.)
- B. 4.25% (w/v) Sodium Chloride Solution
(Prepare 300 ml in deionized water using Sodium Chloride, Sigma Prod. No. S-9625.)
- C. 36 mM Diethyl Barbiturate, 36 mM Sodium Acetate,
0.85% (w/v) Sodium Chloride Solution, pH 7.35 at 25°C (Soln B)
(Prepare 1 liter by combining 250 ml of Reagent A, 200 ml of Reagent B, 217 ml of 0.1 M HCl, and 333 ml of deionized water. Adjust the pH to 7.35 at 37°C with either 1 M HCl or 1 M NaOH.)
- D. 25.7 mM Sodium Citrate Solution
(Prepare 100 ml in deionized water using Citric Acid Trisodium Salt, Dihydrate Sigma Prod. No. C-7254.)
- E. 0.85% (w/v) Sodium Chloride Solution (NaCl)
(Prepare 300 ml in deionized water using Reagent B.)

Enzymatic Assay of THROMBIN (EC 3.4.21.5)

REAGENTS:

- F. 7.2 mM Diethyl Barbiturate, 7.2 mM Sodium Acetate, 5.1 mM Sodium Citrate, 0.68% (w/v) Sodium Chloride, 1.0% (w/v) Bovine Serum Albumin, and 0.5% (w/v) Polyethylene Glycol (Enz Dil)
(Prepare 500 ml by combining 100 ml of Reagent C, 100 ml of Reagent D, 300 ml of Reagent E, Albumin Bovine, Sigma Prod. No. A-4378, and Polyethylene Glycol Sigma Prod. No. P-2139.)
- G. Plasma Solution (Plasma)
(Immediately before use, reconstitute 2.0 ml of Human Plasma, lyophilized with 2 ml of deionized water. Then add 2 ml of Reagent E. Keep at room temperature.)
- H. Thrombin Enzyme Solution (Thrombin)
(Immediately before use, reconstitute Thrombin vial with 1 ml of deionized water. Further dilute to 2.7 - 5.1 units/ml of Thrombin in Reagent F, in glass tubes. Serial dilutions should be made in Reagent F so that clotting times are between 15 - 25 seconds. If the clotting time recorded is too long, increase the Thrombin concentration. If the time recorded is too short, decrease the Thrombin concentrations. Subsequent dilutions are also to be made in glass tubes.)
- I. NIH Thrombin Standard Solution (Std)
(Use Thrombin Reference Standard (Lot J) which has been diluted in Reagent F. Note: Current Standard Curve has been made with N.I.H. Thrombin standard diluted in glass test tubes. Next standard curve (late 1995) will use Plastic test tubes.)

PROCEDURE:

Step 1:

Pipette (in milliliters) the following reagents into fibrometer cups containers, which have been pre-warmed to 37°C.

	<u>Test</u>
Reagent G (Plasma)	0.20
Allow to stand at 37°C for thirty seconds. Then add:	
Reagent H (Thrombin)	0.10

Enzymatic Assay of THROMBIN (EC 3.4.21.5)

PROCEDURE: (continued)

Record the clotting time using a suitably thermostatted fibrometer. A 0.3 ml Fibrometer probe should be used.

Compare the clotting times of the Tests against a NIH Standard curve for Thrombin clotting times versus units of Thrombin/ml.

Determine the units of Thrombin of the Test from the Standard Curve.

CALCULATIONS:

Units/ml enzyme = (Units of Thrombin from Std Curve)(df)

df = Dilution factor

$$\text{Units/mg solid} = \frac{\text{units/ml enzyme}}{\text{mg solid/ml enzyme}}$$
$$\text{Units/mg protein} = \frac{\text{units/ml enzyme}}{\text{mg protein/ml enzyme}}$$

UNIT DEFINITION:

Activity is expressed in NIH units obtained by direct comparison to a NIH Thrombin Reference Standard, Lot J.

FINAL ASSAY CONCENTRATIONS:

In a 0.30 ml reaction mix, the final concentrations are 33% (v/v) plasma, and 0.27 - 0.50 unit thrombin (components of the enzyme diluent are not included).

REFERENCE:

Human Blood Coagulation, Haemostasis, and Thrombosis (1976) p. 721-722, 2nd ed., R. Biggs, ed., Blackwell Scientific Publications, Philadelphia, PA

NOTES:

1. Standards should be used immediately and kept on ice after they are dissolved.

**Enzymatic Assay of THROMBIN
(EC 3.4.21.5)**

NOTES: (continued)

2. This assay is based on the cited reference.
3. Where Sigma Product or Stock numbers are specified, equivalent reagents may be substituted.

Sigma warrants that the above procedure information is currently utilized at Sigma and that Sigma products conform to the information in Sigma publications. Purchaser must determine the suitability of the information and products for its particular use. Upon purchase of Sigma products, see reverse side of invoice or packing slip for additional terms and conditions of sale.