

ElectroGreen™ Solvents for Electronics


**Smarter, safer, and more
sustainable solvents**

Tailored to support your electronics and energy applications responsibly, for sustainable development.

We offer greener solvent blends with rigid specifications - a simple reliable switch without compromising the environment!

Our products offer:

- High purity (GC)
- Low residue in evaporation (RESE)
- Low metal content (ICP)
- Low water content (KF)
- Low acidity
- Low toxicity and VOC
 - enabling solution-processable techniques outside of fumehood
- Accessible cost



Explore our new line of Green solvent blends for energy and electronics applications at SigmaAldrich.com/Electrogreen












Greener solvents for energy and electronic applications

Dedicated to supporting the demanding specifications for energy and electronics responsibly, by offering:

- Bio-based replacements
- Reduced toxicity
- Reduced carbon footprint

Superior performance through sustainable technologies!

Cat. No.	Product Name		Relative Evaporation Rate	Hansen Dispersion	Solubility Polar	H Bonding Parameter
929670	ElectroGreen™, Acetone substitute for electronics, bio-sourced		2.84	7.7	3.4	6.1
929697	ElectroGreen™, Butyl Cellosolve substitute for electronics, bio-sourced		0.11	7.5	3.8	6.1
929735	ElectroGreen™, Cyclohexanone substitute for electronics, bio-sourced		0.25	7.7	3.5	6.4
929654	ElectroGreen™, Isopropyl Alcohol substitute for electronics, bio-based		1.24	7.7	4.2	8.8
929727	ElectroGreen™, Methyl Amyl Ketone substitute for electronics, bio-sourced		0.247	7.7	3.4	6.7
929719	ElectroGreen™, NMP substitute for electronics - type 1, bio-sourced		<0.05	8.8	5.9	3.7
929662	ElectroGreen™, NMP substitute for electronics - type 2, bio-sourced		< 0.02	9	6.8	4.6
929689	ElectroGreen™, Toluene substitute for electronics, bio-sourced		2.57	7.7	2.8	6
929700	ElectroGreen™, Xylene substitute for electronics, bio-sourced		0.89	7.7	3.1	5.8

We offer you alternatives to hazardous solvents as more regulations are enforced.

Tailored for reliable electronic applications, to minimize environmental impact.

For full product list go to

SigmaAldrich.com/Electrogreen



To place an order or receive technical assistance in Europe, please call Customer Service:
France: 0825 045 645 Spain: 901 516 645 Option 1
Germany: 069 86798021 Switzerland: 0848 645 645
Italy: 848 845 645 United Kingdom: 0870 900 4645

For other countries across Europe, please call: +44 (0) 115 943 0840
Or visit: MerckMillipore.com/offices
For Technical Service visit: MerckMillipore.com/techservice

Merck KGaA
Frankfurter Strasse 250
64293 Darmstadt, Germany

MerckMillipore.com

We have built a unique collection of life science brands with unrivalled experience in supporting your scientific advancements.

Millipore® Sigma-Aldrich® Supelco® Milli-Q® SAFC® BioReliance®

© 2023 Merck KGaA, Darmstadt, Germany and/or its affiliates. All Rights Reserved. Merck, the vibrant M, BioReliance, Millipore, Milli-Q, SAFC, Sigma-Aldrich, Supelco, and ElectroGreen are trademarks of Merck KGaA, Darmstadt, Germany or its affiliates. All other trademarks are the property of their respective owners. Detailed information on trademarks is available via publicly accessible resources.

MK_FL12276EN 48038 05/2023

