

# Using Supel™ QuE Verde for QuEChERS and SLB®-5ms GC Column

One potential approach for the determination of pesticide residues in cannabis is the use of the "quick, easy, cheap, effective, rugged and safe" (QuEChERS) method outlined in AOAC official method 2007.01. In this application, QuEChERS was used in the extraction of pesticides from dried cannabis. For cleanup of the extracts, two different sorbent mixes were evaluated

# **Experimental**

Dried cannabis was supplied courtesy of Dr. Hari H. Singh, Program Director at the Chemistry and Physiological Systems Research Branch of the National Institute on Drug Abuse at the National Institute of Health. The sample was ground to a fine powder and extracted following the procedure outlined in the condition section of Figure 1. The resulting acetonitrile extract was cleaned using two different sorbents: (1) PSA/C18/ENVI-Carb™ and (2) Supel QuE Verde. Unspiked and spiked (50 ng/g) samples were prepared. Analysis of the final extracts was done by GC/MS/MS using the GC conditions listed in Figure 1. Quantitation was performed against multi-point, matrix-matched calibration curves prepared in unspiked cannabis extract. Separate curves were prepared for each cleanup sorbent.

### **Results and Discussion**

#### **Matrix Removal**

Figure 2 shows cannabis extracts before and after each cleanup. As expected, the PSA/C18/ENVI-Carb sorbent mixture removed the most color. The Supel QuE Verde mix removed the green from the cannabis extract, leaving only yellow pigments, and a much lighter colored extract than no cleanup. Extracts were analyzed by GC/MS in full scan mode to evaluate background (Figures 1 a-c). The TIC patterns of the extracts, cleaned and uncleaned, appear similar. However, there are some differences in peak amplitude between the chromatograms, and if the sum of the peak areas in the TICs are compared, it is evident that the lowest background was obtained using Supel QuE Verde cleanup.

Figure 2. QuEChERS Extracts of Cannabis With and **Without Cleanup** 







Figure 1. GC/MS Scan Analysis of Cannabis Extract Background (a) with no cleanup, (b) after cleanup with Supel QuE PSA/C18/ENVI-Carb, and (c) after cleanup with Supel QuE Verde

sample/matrix: ground cannabis, 1 gm add 10 mL water to sample, allow to sit for 30 min sample pretreatment:

extraction tube: Supel QuE Citrate extraction tube (55227-U) add 10 mL of acetonitrile containing 1% acetic acid; shake extraction process:

10 min at 2,500 rpm on automated shaker; add contents of Supel QuE citrate extraction tube; shake 1 min; centrifuge

at 5,000 rpm for 5 min; remove supernatant cleanup tube: Supel QuE Verde, 2 mL cleanup tube (55447-U) cleanup process:

transfer 1 ml of supernatant to Supel OuF Verde cleanup tube; shake for 2 min; centrifuge at 5,000 rpm for 5 min; remove supernatant and place in amber low adsorption

vial for GC/MS/MS analysis. column: SLB\*-5ms, 30 m  $\times$  0.25 mm I.D., 0.25  $\mu$ m (28471-U)

50 °C (2 min), 8 °C/min to 320 °C (5 min) oven:


inj. temp.: detector:

250°C MSD, full scan, m/z 45-500

MSD interface: 320 °C

carrier gas: helium, 1.4 mL/min constant injection: 1 μL, splitless (splitter open at 0.75 min)

4 mm l.D., split/splitless type, single taper wool packed FocusLiner™ design (2879901-U)





110 ■ Supel QuE PSA/C18/ENVI-Carb ■ Supel QuE Verde 100 90 80 % Recovery 70 60 50 40 30 20 10 Tetathormohos , weldbutanil PRETON DITORDE Paclobutatol Malathion CARUTTAIN Cypernethin Tifloxystobin Tebucaratale Tettanethin Methorychia Etokalole Outrophen **Pesticides** 

Figure 3. Average Pesticide Recoveries and Relative Standard Deviation (RSD) Values for Spiked Replicates of Cannabis (n=3)

# Recovery and Reproducibility

The average recoveries obtained from 50 ng/g spiked cannabis samples are summarized in Figure 3. Recoveries were generally better using the Supel QuE Verde cleanup for many of the pesticides, especially the pyrethroid pesticides and triazole fungicides. The organophosphorus pesticides showed mixed results, with some such as chloropyrifos showing better recovery from Supel QuE Verde, and others such as phosmet showing better recovery using PSA/C18/ENVI-Carb. Quinoxyfen showed very poor recovery after cleanup with PSA/C18/ENVI-Carb. This compound has some planar character to its structure, which resulted in strong retention on the ENVI-Carb, and thus reduced recovery. The pesticide synergist piperonyl butoxide, of interest in relation to cannabis production, showed >70% recovery using both cleanups, but better recovery after Supel QuE Verde compared to PSA/C18/ENVI-Carb cleanup. Reproducibility, determined as % RSD for n=3 spiked replicates, was generally very good for both cleanups. The exceptions were tetramethrin and cypermethrin, which had RSD values >20% after PSA/C18/ENVI-Carb cleanup.

# Conclusions

As demonstrated here, QuEChERS is a viable approach for the analysis of pesticide residues in cannabis. Many compounds of interest, including piperonyl butoxide, show good recovery and reproducibility by this extraction technique. For cleanup of QuEChERS extracts of

cannabis, the use of graphitized carbon is recommended for removal of chlorophyll. However, as evidenced by the recovery of quinoxyfen in **Figure 3**, traditional GCBs such as ENVI-Carb will reduce the recovery of pesticides with planar structures. Supel QuE Verde, which contains PSA, Z-Sep+ and an improved GCB, can be used to reduce pigmentation while improving recoveries of these compounds.

Compared to conventional PSA/C18/GCB cleanup, cannabis extracts cleaned with the Supel QuE Verde mixture showed lower GC/MS background, and better recoveries for many pesticides.

#### **Featured Products**

Description	Cat. No.
Supel™ QuE QuEChERS Products	
Verde Cleanup Tube, 2 mL, 100 ea	55447-U
PSA/C18/ENVI-Carb (AOAC) Tube, 2 mL, 100 ea	55289-U
Citrate Extraction Tube, 12 mL, 50 ea	55227-U
Empty Centrifuge Tube, 50 mL, 50 ea	55248-U
Column	
SLB-5ms Capillary GC Column 30 m × 0.25 mm l.D., 0.25 μm	28471-U

Visit our cannabis testing resources at **sigma-aldrich.com/cannabis** 

Order/Customer Service: sigma-aldrich.com/order
Technical Service: sigma-aldrich.com/techservice
Development/Custom Manufacturing Inquiries SAFC' safcglobal@sial.com
Safety-related Information: sigma-aldrich.com/safetycenter

©2015 Sigma-Aldrich Co. LLC. All rights reserved. SAFC, SIGMA-ALDRICH and SUPELCO are trademarks of Sigma-Aldrich Co. LLC. registered in the US and other countries. SLB is a registered trademark of Sigma-Aldrich Co. LLC. Exhibition Sigma-Aldrich Co. LLC. Exhibition Sigma-Aldrich Website at www.sigmaaldrich.com and/or on the reverse side of the invoice or packing slip. Sigma-Aldrich Corp. is a subsidiary of Merck KGaA, Darrostard Germany.

World Headquarters 3050 Spruce St. St. Louis, MO 63103 (314) 771-5765 sigma-aldrich.com

> RYF 84237 / T415169A 1125