3050 Spruce Street, St. Louis, MO 63103 USA
Tel: (800) 521-8956 (314) 771-5765 Fax: (800) 325-5052 (314) 771-5757
email: techservice@sial.com sigma-aldrich.com

Product Information

Trypsin from bovine pancreas

cell culture tested

Catalog Number **T9935**Storage Temperature -20 °C

CAS RN: 9002-07-7

Enzyme Commission Number (EC): 3.4.21.4

Synonyms: Tryptase, Tryptar, Cocoonase,

Parenzyme, Parenzymol

Product Description

Molecular Weight: 24 kDa^{1,2}

Extinction Coefficient: $E^{1\%} = 12.9 - 15.4 (280 \text{ nm})^{3.4}$

pl: 10.1 - 10.5^{2,5}

Trypsin consists of a single chain polypeptide of 223 amino acid residues. Trypsin is produced by the removal of the N-terminal hexapeptide from trypsinogen which is cleaved at the Lys 6 - Ile^7 peptide bond. The amino acid sequence of trypsin is crosslinked by 6 disulfide bridges. This native form of trypsin is referred to as β -trypsin. Autolysis of β -trypsin (which is cleaved at Lys 131 - Ser 132) results in α -trypsin which is held together by disulfide bridges. Trypsin is a member of the serine protease family. The active site amino acid residues of trypsin include His 46 and Ser 183 . 2,3,4

Trypsin will cleave peptides on the C-terminal side of lysine and arginine amino acid residues. The rate of hydrolysis is slower if an acidic residue is on either side of the cleavage site and no cleavage occurs if a proline residue is on the carboxyl side of the cleavage site. The pH optimum of trypsin is 7-9.6 Trypsin will also hydrolyze ester and amide linkages of synthetic derivatives of amino acids such as: benzovl L-arginine ethyl ester (BAEE), p-toluenesulfonyl-L-arginine methyl ester (TAME), tosyl-L-arginine methyl ester, $N\alpha$ -benzoyl-L-arginine p-nitroanilide (BAPNA), L-lysyl-p-nitroanilide, and benzoyl-L-arginamide. 2,7,8 Reported K_m values are BAEE (0.05 mM), TAME (0.05 mM), and BAPNA (0.94 mM). Assuming the pH and temperature are the same and using a molar extinction coefficient of 808 at 254 nm for BAEE, the following conversions are valid:

1 BAEE μ M Unit = 200 BAEE Units 1 TAME μ M Unit = 0.27 BAEE μ M Units 1 BAEE μ M Unit = 3.64 TAME Units 1 TAME μ M Unit = 55 BAEE A₂₅₃ Units 1 BAEE A₂₅₃ Unit = 0.018 TAME μ M Unit 1 TAME μ M Unit = 180 TAME A₂₄₇ Units 1 TAME A₂₄₇ Unit = 0.33 BAEE Units A USP Unit = Δ A₂₅₃ of 0.003 per minute 1 NF Unit = 3.3 A₂₅₃ BAEE Units. 9

The oxidized B chain of insulin is often used as a substrate to determine the suitability of trypsin for use in protein sequencing. The presence of two peptide bonds (Arg²² - Gly²³ and Lys²⁹ - Ala³⁰) make it an ideal peptide for use in this kind of application. ¹⁰

Serine protease inhibitors that will inhibit trypsin include DFP (diisopropyl fluorophosphate), TLCK(N α -p-tosyl-L-lysine chloromethyl ketone), PMSF (phenylmethanesulfonyl fluoride), APMSF (4-amidinophenylmethanesulfonyl fluoride), AEBSEF (4-(2-aminoethyl)benzenesulfonyl fluoride), aprotinin, leupeptin, α_2 -macroglobulin, α_1 -antitrypsin, p-aminobenzamidine, benzamidine (reversible), soybean trypsin inhibitor, lima bean inhibitor, bovine pancreas trypsin inhibitor, chicken egg white inhibitor, and turkey egg white inhibitor.

Precautions and Disclaimer

This product is for R&D use only, not for drug, household, or other uses. Please consult the Material Safety Data Sheet for information regarding hazards and safe handling practices.

Preparation Instructions

This enzyme is soluble in 1 mM HCl (1 mg/ml).

Storage/Stability

Solutions in 1 mM HCI (pH 3) are stable for approximately 1 year when aliquoted and stored at -20 °C. The presence of Ca²⁺(20 mM) will also retard trypsin's ability to self digest itself (autolysis) and will maintain the stability of the trypsin in solution. ^{2,6} Trypsin retains most of its activity in 2.0 M urea, 2.0 M guanidine HCl, or 0.1% (w/v) SDS. ¹³ Trypsin is reversibly denatured at high pH (above 11), by precipitation with TCA, or by high concentrations of urea (greater than 6.5 M). ³ In order to abolish all trypsin activity, heating at 100 °C in 1% (w/v) SDS for 5 minutes is required. ¹⁴

Procedure

Trypsin may be used to remove adherent cells from a culture surface. Cells are most commonly removed from the culture substrate by treatment with trypsin, or trypsin•EDTA. Trypsin 1X solutions can range from 0.025% to 0.5%. The reasons for the range of concentrations are as follows: (1) Differences in trypsin activity or potency; (2) Different incubation times; (3) Different cell lines.

Incubating cells with too high a trypsin concentration for too long a time period will damage cell membranes and kill the cells. If unsure about the concentration of trypsin to use, use a low concentration. There can be lot-to-lot variation in dissociation times which is to be expected since the enzymatic activity of each lot will differ. If trypsin is being solubilized or diluted from a concentrated solution, it is important to use a buffered salt solution that contains no Ca²⁺ or Mg²⁺, such as Hank's Balanced Salt Solution, Modified (Product No. H 9394). Adjust the pH of trypsin solution to 7.4-7.6.

- Remove medium from culture vessel by aspiration and wash the monolayer with Ca²⁺ and Mg²⁺ - free salt solution to remove all traces of serum. Remove salt solution by aspiration.
- Dispense enough trypsin or trypsin•EDTA solution into culture vessel(s) to completely cover the monolayer of cells and place in 37 °C incubator for approximately 2 minutes.
- Remove the trypsin or trypsin EDTA solution by aspiration and return closed culture vessel(s) to incubator. The coated cells are allowed to incubate until cells detach from the surface. Progress can be checked by examination with an inverted microscope.

Note:The time required to remove cells from the culture surface is dependent on cell type, population density, serum concentration in the growth medium, potency of trypsin, and time since last subculture. Trypsin causes cellular damage and time of exposure should be kept to a minimum.

- 4) When trypsinization process is complete the cells will be in suspension and appear rounded.
- 5) It is advisable to add serum or medium containing serum to the cell suspension as soon as possible to inhibit further tryptic activity which may damage cells. Soybean trypsin inhibitor, Catalog Number T9008, can also be added at an equimolar concentration to inhibit the trypsin that is present. Soybean trypsin inhibitor is used when culturing in serum-free conditions.
- 6) Cells can be resuspended by gently pipetting the cell suspension to break up the clumps. Further dilution can be made, if required, for cell counts and/or subculturing.

References

- 1. Cunningham, L. W. Jr., Molecular Kinetic properties of crystalline diisopropyl phosphoryl trypsin. J. Biol. Chem., **211**, 13-19 (1954).
- 2. Walsh, K. A., Trypsinogens and trypsins of various species. Meth. Enzymol., **19**, 41-63 (1970).
- Keil, B., in The Enzymes, 3rd ed., Vol. III, Boyer, P. D., Academic Press (New York, NY: 1971), pp. 250-275.
- Shaw, E, et al., Evidence for an active center histidine in trypsin through use of a specific reagent, 1-chloro-3-tosylamido-7-amino-2heptanone, the chloromethyl ketone derived from N^α-tosyl-L-lysine. Biochemistry, **4(10)**, 2219-2224 (1965).
- Buck, F. F., et al., On the mechanism of enzyme action. LXXII. Studies on trypsins from beef, sheep, and pig pancreas. Arch. Biochem. Biophys., 97, 417-424 (1962).
- Sipos, T., and Merkel, J. R., An effect of calcium ions on the activity, heat stability, and structure of trypsin. Biochemistry, 9(14), 2766-2775 (1970).
- Burdon, R. H., et al., in Laboratory Techniques in Biochemistry and Molecular Biology, Vol. 9, 2nd ed., Allen, G., ed., Elsevier/North (New York, NY: 1989), pp. 73-104.

- 8. Enzyme Handbook, Vol. II, Barman, T. E., Springer-Verlag (New York, NY: 1969), pp. 618-619.
- 9. USP, Vol. 23, p. 1611.
- 10. Wang, S. S., and Carpenter, F. H., Kinetics of the tryptic hydrolysis of the oxidized B chain of bovine insulin. Biochemistry, **6(1)**, 215-224 (1967).
- 11. Proteolytic Enzymes, A Practical Approach, Beynon, R. J., ed., IRL Press (New York, NY: 1989), p. 240.

- 12. Carpenter, F. H., Treatment of trypsin with TPCK. Methods Enzymol., **11**, 237 (1967).
- 13. Methods of Molecular Biology, Vol. 3, Smith, B. J., Humana Press, (New Jersey, 1988), pp. 57-69.
- 14. Porter, W. H., and Preston, J. L., Retention of trypsin and chymotrypsin proteolytic activity in sodium dodecyl sulfate solutions. Anal. Biochem., **66**, 69-77 (1975).

RG,PHC 09/10-1